



Cleaning Instructions

To clean, hand wash in warm soapy water.

This product is dishwasher safe.

Technical Data

Length: 8" (200mm)

Manufactured for and distributed in the UK by:
Glopac Mobility Ltd., Edison Road, Hams Hall, Coleshill, Birmingham B46 1AB

**For more products from the Mobilease daily living aids range,
please visit our website www.mobilease.co.uk**

After Sales Support:

**UK / N. IRELAND HELPLINE NO.
WEB SUPPORT**

**00800 45672245
www.mobilease.co.uk**

Glopac Mobility Ltd. is a member of the British Healthcare Trades Association (BHTA)



Version 1.0



Tap Turner User Instructions




A Mobilease quality
care product

**Prior to use please read all instructions carefully.
Keep instructions in a safe place for future reference.**

**These tap turners are not designed to overcome the difficulties
of turning taps which have become corroded or are very stiff to
use. If this is the case it is recommended that a plumber be
called rather than a tap turner be fitted.**

Mobilease Tap Turner

The highly effective Mobilease tap turner is designed to add a lever action to most types of domestic taps. These tap turners will fit most sizes of crystal or crosshead taps. The long handle gives extra leverage thus providing assistance for people who have difficulty in gripping conventional taps.

Conveniently packaged in a twin-pack with a red tap turner for hot and a blue one for cold water taps, these tap turners are easy to use and fit as well as being highly adjustable.



Using the Mobilease tap turner

The Mobilease tap turner is designed to attach to taps with a simple push-fit and once fitted should be left in position permanently. The lever is pivoted to enable it to be flipped over for situations where the taps are located close to the wall, and to be lifted back to allow full access to the sink or basin.

Non-slip material is used to line the inside of the Mobilease tap turner which grips the tap in use. Too little material will provide insufficient grip so it is important that the fitting instructions are followed carefully.

Inside the head of each tap turner are 3 lengths of non-slip material/tape. Remove all of the non-slip material from the inside of the head of the tap turner.

Using the V-shaped gauge provided determine the size of the tap by placing the gauge over the top of your tap. Dependent upon the size of your tap use the indicated number of strips to insert into the underside of the head of the tap turner making sure the tape sits snugly inside the head.

Now push the tap turner onto the tap remembering to colour code correctly, i.e. blue for cold water and red for hot water taps.

Should it be a little difficult to push the tap turner into position, moisten the head of the tap slightly.

In the unlikely event that the tap turner slides without turning the tap at the same time, add a little extra of the non-slip material.

Ensure that the tap turners are installed at the correct angle to turn your water taps.

Safety and Maintenance Instructions

The Mobilease tap turner is not designed to open corroded taps or taps which are generally very stiff to open or close.

Always turn the tap turner slowly taking care not to burn yourself on hot water.

